



## **PDI** **13 - Inch** **Television**

*A personal color TV designed specifically for hospitals and nursing homes.*

*This set is available with PDI Top Mount or Shelf Mounts.*

*This set can be operated with a standard Single Button Pillow Speaker or Digital Pillow Speaker.*

*Built-in closed captioning device.*

### **PDI Communication Systems**

*Division of  
Precision Industries Incorporated  
40 Greenwood Lane  
Springboro, Ohio 45066  
PH:937-743-6010/1-800-628-9870  
FAX:937-743-5664*

*<http://www.pdiarm.com>  
E-mail: [pdi@pdiarm.com](mailto:pdi@pdiarm.com)*

# PDI Z13TVB-WR

## 13" - Inch TV

Standard conversion allowing television to be operated by pillow speaker from patient bedside. Can be used with the following pillow speakers:

### **CURBELL**

#103-001-Single Button

#1031-001-Gen II Digital

#31031-001-Gen III Digital

### **MEDTEK**

#A1833-Single Button

#A1833-083T-Single Button

#A1873-085T-Digital

Television must be programmed with infrared remote

#PDI108-203-13

## **FEATURES:**

### **Trilingual On-Screen Menu Displays**

Easily access Zenith's convenience features and audio/video settings through the remote control or front panel controls. Adjustments are confirmed on screen as you make them. Choose English, French or Spanish language menus.

### **Multi-Purpose Timer**

Can be used as an automatic:

- Wake-up Timer

- Turn-off Timer

- Sleep Timer which lets you set the TV for automatic turn-off in increments up to 2 hours.

### **CaptionVision (CC) Capability**

Enjoy closed captions and other information (text) broadcast with many TV programs, or on many videotape movies. Ideal for the hearing impaired, children learning to read, those learning English, Spanish, or for quiet late night TV viewing.

### **Protected Memory**

Integral memory retains all video settings when TV is turned off or when power is interrupted.

### **Pillow Speaker Control**

This set will use a single or multi-button digital pillow speaker using existing 3-wire cross room wiring. Channel UP/DOWN, ON/OFF, CC, Mute\*. **Connect via a standard 1/4" stereo plug.**

\*Functions dependent on pillow speaker.

### **Channel Add/Erase**

Delete unwanted or seldom viewed channels or add new channels at any time via IR set-up remote. (P/N PD108-206-13)

### **1-1/2" x 3-1/2" Oval Speaker**

Acoustically designed to cabinet.

### **Screen Size:**

13" Diagonal

### **Dimensions:**

13-1/4"H, 14-1/2"W, 14-3/8"D

### **Net Weight:**

22 lbs.

### **Shipping Weight:**


16 lbs.

### **Power Source:**

120V AC, 60Hz

### **Hospital Grade 3-Prong Clear Plastic Plug**

This set is available with the optional PDI Top Mount for use with standard PDI-178 Wall Brackets.



Studs are provided in the bottom of the TV for mounting on the PDI Shelf Mounts or other TV mounts.

### **PDI Communication Systems**

Division of  
Precision Industries Incorporated  
40 Greenwood Lane  
Springboro, Ohio 45066  
PH:937-743-6010/1-800-628-9870  
FAX:937-743-5664

<http://www.pdiarm.com>  
E-mail: [pdi@pdiarm.com](mailto:pdi@pdiarm.com)